

One-Light LED Mini-Pendant

Ceiling cord mounted • Dry location listed



Description:

Inspired by beautiful glass forms commonly found in a science lab, Beaker has a heightened sense of modern industrial styling. The 9W LED source offers energy efficient and cost savings benefits, while the industrial-inspired design complements a variety of mid-century modern interior designs. The one-light woven cloth cord hung mini-pendant has champagne glass with an Antique Bronze frame.

Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- Champagne glass shade, White acrylic Diffuser
- LED Module is replaceable (part # 93054049)
- Inspired by beautiful glass forms commonly found in a science lab.
- Heightened sense of modern industrial styling.
- Vessels are suspended from herringbone cloth cords.
- Dimmable to 10% with many ELV dimmers
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 10 feet of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	249/34.6 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry location listed ENERGY STAR® qualified

P5345-2030K9

Images:



Dimensions:

Diameter: 10-1/4"
 Height: 11-1/2"
 Overall Ht. W/Chain: 121-1/2"

Glass
 Width: 10-3/16"
 Length: 10-3/16"
 Height: 8-11/16"
 Glass 2
 Width: 2-15/16"
 Length: 2-15/16"
 Height: 0-11/16"

Photometrics:

P5345-2030K9

ELECTRICAL DATA	P5345-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.075 A
Input Power	9
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P5345-2030K9


LED Light Engine: 3000 K 90+
 System Wattage: 9
 Fixture delivered lumens: 249
 Fixture Efficacy: 34.6
 Spacing Criteria: 1.1

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	160	
5	150	14
15	133	38
25	122	56
35	108	64
45	44	36
55	14	14
65	11	11
75	6	8
85	3	3
90	1	
95	1	1
105	1	1
115	1	1
125	0	0
135	0	0
145	0	0
155	0	0
165	1	0
175	1	0
180	1	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	108	43.5
0-40	173	69.4
0-60	222	89.3
0-90	244	98.2
90-120	3	1.3
90-130	4	1.5
90-150	4	1.6
90-180	5	1.8
0-180	249	100.0



Test 16.00184 Test Date 1/20/16

P5345-2030K9

Dimming Notes:

P5345 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.