

Z-2010 LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Z-2010 LED Collection Oil Rubbed Bronze One-Light LED Outdoor Wall Sconce

Specifications:

- Etched Glass Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 0.75 in ht., 4.75 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	670/71 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed Meets California Title 24 JA8-2016

P560132-108-30



Dimensions:

Width: 12 in
Depth: 2-3/16 in
Height: 12 in
H/CTR: 6 in

Etched Glass Shade
Width: 3-1/2 in
Height: 3-1/2 in


P560132-108-30

Photometrics:

ELECTRICAL DATA	P560132-108-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.079
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P560132-108-30

LED Light Engine: 3000 K 90 CRI
 System Wattage: 9
 Fixture delivered lumens: 88
 Fixture Efficacy: 9.3
 Spacing Criteria:



Test 19.01082 Test Date 06/17/19

CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION					FLUX
CANDELA	DISTRIBUTION					
0.0	45.0	90.0	135.0	180.0		
0	0.2	0.2	0.2	0.2	0.2	
5	13.1	7.1	0.1	0.2	0.5	0.5
15	23.8	25.8	0.4	6.3	22.3	4.1
25	12.6	21.0	0.0	25.1	26.9	7.8
35	1.8	12.6	0.2	26.9	22.7	9.1
45	0.9	4.1	0.3	25.2	16.1	9.4
55	0.6	1.5	0.5	22.4	10.3	9.3
65	0.0	0.4	0.2	19.0	5.3	8.2
75	0.4	0.9	0.7	17.6	4.9	7.7
85	0.0	0.6	0.5	15.7	4.1	7.0
90	0.0	0.5	0.3	15.1	3.3	
95	0.0	0.5	0.5	14.8	3.5	6.3
105	0.0	0.5	0.3	14.2	3.3	5.4
115	0.1	0.6	0.4	11.7	3.0	4.6
125	0.6	0.8	0.3	6.2	4.5	3.5
135	0.4	2.0	0.2	1.7	3.3	2.1
145	1.0	6.3	0.0	0.8	1.1	1.4
155	3.6	6.4	0.0	0.4	0.4	1.1
165	5.1	3.3	0.1	0.7	0.4	0.4
175	0.0	0.1	0.1	0.1	0.1	0.0
180	0.0	0.0	0.0	0.0	0.0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	12.4	14.1
0-40	21.6	24.5
0-60	40.2	45.7
0-90	63.2	71.8
90-120	16.3	18.5
90-130	19.8	22.5
90-150	23.2	26.4
90-180	24.8	28.2
0-180	88.0	100.0

P560132-108-30

Dimming Notes:

P560132-108-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Caseta

Lutron_Ariadni AY-600P

Leviton_Illumatech IPI06-1LZ

Leviton_SureSlide 6672

Lutron_Ariadni AYCL-153P

Lutron_Skylark Contour CTCL-153P

Lutron_Diva DVCL-153P

Lutron_Toggler TGCL-153P

Lutron_Maestro MACL-153M

Lutron_Ariadni AYLV-600P

Lutron_Nova T NTLV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Leviton_Renoir II AWRMG-EAW

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.