

Project:			
Fixture Type:			
Location:			
Contact:			

P560150-031

Irondale

Incorporate memorable, modern lighting with this industrial lantern. A matte black frame attaches to a rectangular wall plate. A clear glass shade harbors an etched glass diffuser inside ready to provide a lovely ambient glow.

- A clear glass shade harbors an etched glass diffuser inside ready to provide a lovely ambient glow.
- · A matte black frame attaches to a rectangular wall plate.
- Incorporate memorable, modern lighting with this industrial lantern.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- Perfect for urban industrial or Craftsman settings.
- · Measures 9-inch width by 18-1/2-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Steel Construction

Glass/Shade: Clear glass Curved Panel, Etched White glass Cylindrical



Width: 9 in Height: 18-1/2 in Depth: 10-1/2 in H/CTR: 16 in

Clear glass Curved Panel

Width: 2-5/8 in Height: 15 in

Etched White glass Cylindrical

Width: 5-1/2 in Height: 15-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Swivel mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 10.25" ht., 0.75" depth			