

## Z-2025 LED

 Ceiling Mounted • Wet Location Listed **PROGRESS LED**

### Description:

Z-2025 LED Collection One-Light Satin White Modern Style Indoor/Outdoor Wall Light

### Specifications:

- Frosted Glass Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 0.75 in ht., 4.75 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	670/71 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	Meets California Title 24 JA8-2016


## P560259-028-30



### Dimensions:

Width: 6-1/4 in  
 Extends: 2-1/4 in  
 Height: 6-1/4 in

Frosted Glass Cylindrical  
 Width: 1-1/4 in  
 Height: 4-3/4 in



# P560259-028-30

## Dimming Notes:

---

P560259-028-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva\_DVELV-300P

Lutron\_Nova\_T\_NTELV-300

Lutron\_Caseta\_

Lutron\_Ariadni\_AY-600P

Leviton\_Illumatech\_IPI06-1LZ

Leviton\_SureSlide\_6672

Lutron\_Ariadni\_AYCL-153P

Lutron\_Skylark\_Contour\_CTCL-153P

Lutron\_Diva\_DVCL-153P

Lutron\_Toggler\_TGCL-153P

Lutron\_Maestro\_MACL-153M

Lutron\_Ariadni\_AYLV-600P

Lutron\_NOVA\_T\_NTLV-600

lutron\_Maestro\_MAEV-600

Lutron\_spacer/system\_SPSELV-600

Lutron\_Renoir\_IL\_AWRMG-EAW

Lutron\_Nova\_N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.