

# Cylinders

Wall Mounted • Wet Location Listed **PROGRESS LED**

## Description:

3" Wall Mount Downlight Cylinder

## Specifications:

- Clear Glass Lens
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.4375 in W., 4.4375 in ht., 1.015 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

## Performance:


Number of Modules	1Cylinder
Input Power	12 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,027/85 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	40 °C
Warranty	5-year Limited Warranty
Labels	CSA Wet Location Listed
	Meets California Title 24 JA8-2016

# P563000-030-30K



## Dimensions:

Width: 4-1/2 in  
 Height: 5-5/8 in  
 Depth: 5-1/2 in  
 H/CTR: 3 in



# P563000-030-30K

**Photometrics:**

<b>ELECTRICAL DATA</b>	<b>P563000-030-30K</b>
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.102 A
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-10 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	


**P563000-030-30K**  
 LED Light Engine: 3000 K 90 CRI  
 System Wattage: 12  
 Fixture delivered lumens: 1027  
 Fixture Efficacy: 85  
 Spacing Criteria: 1.3

**CANDELA DISTRIBUTION**

DEG	CANDELA	LUMENS
0	471	
5	468	45
15	454	128
25	427	197
35	374	232
45	262	201
55	137	124
65	59	61
75	26	28
85	11	11
90	0	

**ZONAL LUMEN SUMMARY**

ZONE	LUMENS	%FIXT
0-30	369	36.0
0-40	602	58.6
0-60	927	90.3
0-90	1027	100.0
90-180	0	0.0
0-180	1027	100.0



Test 17.02583 Test Date 09/28/17

# P563000-030-30K

## Dimming Notes:

---

P563000-030-30K is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Caseta Wireless

Leviton\_SureSlide 6672

Lutron\_Ariadni AYCL-153P

Lutron\_Toggler TGCL-153PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.