

LED Sq Cylinder

 Wall Mounted • Damp Location Listed **PROGRESS LED**

Description:

6" LED Square Cylinder with heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Antique Bronze finish. Wet location listed when used with P860047 top cover lens (sold separately).

Specifications:

- Antique Bronze finish.
- Ideal for a wide variety of interior and exterior applications.
- Die-cast aluminum construction with durable powder coated finish
- 3731 lumens 61.8 lumens/watt per module (delivered)
- 3000K color temperature, 90+ CRI
- Wet location listed when used with P860047 top cover lens (sold separately)
- Dimmable to 10% with many ELV dimmers
- Meets California Title 24 for outdoor use only.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.03 in W., 3.995 in ht.,
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	2
Input Power	29 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	3,731/61.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cULus Damp Location Listed

P5644-20-30K



Dimensions:

Width: 6 in
 Height: 18 in
 Depth: 8-7/8 in
 H/CTR: 8 in

P5644-20-30K

Dimming Notes:

P5644-20-30K is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Leviton_Renoir II AWRMG-EAW

Leviton_6615-P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.