

Project:
Fixture Type:
Location:

Cylinder

Wall Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

5" LED up down wall cylinder - wall lantern in Antique Bronze. The P5675 Series are ideal for a wide variety of interior and exterior applications including residential and commercial. The Cylinders feature a 120V alternating current source and eliminates the need for a traditional LED driver. This modular approach results in an encapsulated luminaire that unites performance, cost and safety benefits. Specify P860045 top cover lens for use in wet locations.

Specifications:

- · Antique Bronze finish.
- · Powder coat finish.
- · Die-cast aluminum construction with durable powder coated finish
- 1,100 lumens 26 lumens/watt per module (delivered)
- 3000K color temperature, 90+ CRI
- · Meets California Title 24 high efficacy requirements for outdoor use only.
- · Dimmable to 10% with many ELV dimmers
- · Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" recessed outlet box: 4.5 in W., 4.5 in ht., 2.95 in depth
- · Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	2
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Down-Source)	795/46 (LM-82) per module
Lumens/LPW (Up-Source)	795/46 (LM-82) per module
Lumens/LPW (Source)	795/46 (LM-82)
Lumens/LPW (Delivered)	1,100/26 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed

P5675-20/30K



Dimensions:

Width: 5 in Height: 14 in Depth: 8-7/8 in H/CTR: 8 in



Cylinder

Photometrics:

Wall Mounted • Damp Location Listed PROGRESS LED

P5675-20/30K

ELECTRICAL DATA P5675-20/30K

Input Voltage 120 V
Input Frequency 60 Hz
Power Factor 0.931
THD <20%

EMI/RFI FCC Title 47, Part 15, Class B


Operating Temperature $-30 \,^{\circ}\text{C}$ to $30 \,^{\circ}\text{C}$ Dimming Yes*

Over-voltage, over-current, short-circuit protected *See Dimming Notes for more information

P5675-20/30K

LED Light Engine: 3000 K 90 CRI

System Wattage: 17 Fixture delivered lumens: 817 Fixture Efficacy: 23.7 Spacing Criteria: 0.94



Test 17.02767 Test Date 10/31/17

CANDELA	DISTR	RIBUTIO	N	
DEG	CANDELA		LUMENS	
0	446			
5	444	42		
15	413	11525	304	139
35	187	117		
45	98	76		
55	28	26		
65	5	5		
75	1	1		
85	1	1		
90	0			
95	0	0		
105	0	0		
115	0	0		
125	0	0		
135	0	0		
145	20	23		
155	265	114		
165	416	114		

458 43

465

175

180

ZONAL LUMEN SUMMARY %FIXT ZONE LUMENS 0-30 296 36.3 50.6 0-40 413 0-60 515 63.1 63.9 0-90 522 90-120 0 0.0 90-130 0.0 2.8 90-150 23 36.1 90-180 295 0-180 817 100.0



Fixture Type:		
Location:		

Cylinder

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P5675-20/30K

P5675-20/30K is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Leviton_Renoir II AWRMG-EAW

Leviton_6615-P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.