

Project:		
Fixture Type:		
Location:		
Contact:		

One-Light Wall Lantern

Wall vertical only mounted • Wet location listed PROGRESS LED





Description:

Clean lines are up front and center for these modern LED outdoor sconces. Valera features a die-cast aluminum frame and matte white, acrylic diffuser. Energy efficient LED source offers 3000K color temperature and 90+CRI output. Title 24 compliant. One-light 17w LED wall lantern in an Antique Bronze finish.

Specifications:

- · Architectural Bronze (-129) (painted)
- · Aluminum Construction
- · Matte White acrylic diffuser
- LED Module is replaceable (part # 93053641)
- · Modern LED outdoor sconce.
- · Clean lines are central to design.
- · Features a die-cast aluminum frame and matte white, acrylic diffuser.
- 1,211 lumens 71.2 lumens/watt per module (source)
- · 3000K color temperature, 90+ CRI.
- Wall mount vertical only.
- Dimmable to 10% brightness (See Dimming Notes)
- Chassis covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- · Complies with "Americans with Disabilities Act" ADA
- · ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1	
Input Power	17w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW (Source)	1211/71.2 (LM-82)	
Lumens/LPW (Delivered)	580/33.9 (LM-79)	
CCT	3000 K	
CRI	90+	
Life (hours)	60,000 (L70/TM-21)	
FCC	Meets FCC Title 47, Part 15 Class B	
Min. Start Temp	-30 ℃	
Max. Operating Temp	30 ℃	
Warranty	5 year warranty	
Labels	cCSAus Wet location listed	
	ENERGY STAR® qualified	
	Meets California Title 24 high efficacy requirements	
	for outdoor use only	

P5801-12930K9

Images:



Dimensions:

Width: 8-5/8" Depth: 4" Height: 11" H/CTR: 5-1/2"

Glass Width: 3-3/4" Length: 8-3/8" Height: 10-15/16"



One-Light Wall Lantern

Wall vertical only mounted • Wet location listed PROGRESS LED



P5801-12930K9

Dimming Notes:

P5801 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.