

One-Light Close-To-Ceiling

 Ceiling ctc mounted • Damp location listed **PROGRESS LED**


Description:

Craftsman styling marries traditional and rustic details. Artistic glass with die-cast aluminum powder coated finish. This one-light LED flush mount is 3000K, 90+ CRI and 1,211 lumens 71.2 lumens/watt per module (source).

Specifications:

- Antique Bronze (-20) (powder coat paint)
- Aluminum Construction
- Etched Seedy Umber Watermark glass shade, Etched Seedy Umber Watermark glass bottom panel
- LED Module is replaceable (part # 93053641)
- Marriage of traditional and rustic styling.
- Artistic glass.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	556/33.1 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 high efficacy requirements for outdoor use only

P6017-2030K9

Images:



Dimensions:

Square: 10"
Height: 5-1/2"

Glass
Width: 8-7/8"
Length: 8-7/8"
Height: 3-11/16"
Glass 2
Width: 8-1/8"
Length: 8-1/8"
Height: 0-1/8"

Photometrics:

P6017-2030K9

ELECTRICAL DATA	P6017-2030K9
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.142 A
Input Power	17
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P6017-2030K9

LED Light Engine: 3000 K 90 CRI

System Wattage: 17

Fixture delivered lumens: 556

Fixture Efficacy: 33.1


Spacing Criteria: 1.1

CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	184	
5	183	17
15	171	48
25	148	68
35	121	76
45	96	74
55	77	69
65	60	60
75	43	45
85	25	28
90	19	
95	17	18
105	15	15
115	13	13
125	12	10
135	9	7
145	7	4
155	4	2
165	2	0
175	0	0
180	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	134	24.0
0-40	209	37.6
0-60	352	63.3
0-90	485	87.2
90-120	47	8.4
90-130	57	10.3
90-150	69	12.4
90-180	71	12.8
0-180	556	100.0



Test 15.00509 Test Date 3/30/15

P6017-2030K9

Dimming Notes:

P6017 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vienti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.