

ONE-LIGHT LED WALL SCNCE

Wall mounted • Dry location listed



Description:

An elegant white linen shade that is open on the top and bottom diffuses light efficiently. Ideal for vanity and hospitality applications.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel Construction
- White linen shade
- LED Module is replaceable (part # 93074037)
- 624 lumens 66 lumens/watt (source)
- 3000K color temperature, 90+ CRI
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
Lumens/LPW (Delivered)	302/32.5 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P710010-129-30

Images:



Dimensions:

Width: 6-3/4"
Depth: 4"
Height: 12"
H/CTR: 6"

Photometrics:


P710010-129-30

ELECTRICAL DATA	P710010-129-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.075 A
Input Power	9
Power Factor	Greater than 0.90
THD	<20%
FCC	Meets FCC Title 47, Part 15 Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*

*See Dimming Notes for more information

P710010-129-30

LED Light Engine: 3000 K 90+
 System Wattage: 9
 Fixture delivered lumens: 302
 Fixture Efficacy: 32.5
 Spacing Criteria: 2 | 2 | 0.1



Test 16.02340 Test Date 09/02/16

CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION					FLUX	
	0.0	45.0	90.0	135.0	180.0		
0	22.8	22.8	22.8	22.8	22.8		
5	31.9	30.2	24.3	12.5	6.6	2.2	
15	51.3	44.5	28.3	13.9	16.4	8.4	
25	73.2	60.5	33.1	16.3	3.4	16.5	
35	62.0	71.9	33.3	11.2	1.6	21.9	
45	32.0	53.3	30.6	10.7	1.7	20.7	
55	20.8	28.4	22.3	9.0	2.1	15.6	
65	23.1	18.9	16.2	7.1	2.3	13.5	
75	24.8	19.4	11.8	5.6	2.6	13.2	
85	25.3	19.2	8.4	4.3	2.5	12.5	
90	25.2	18.9	7.3	3.8	2.3		
95	26.2	19.9	8.6	4.7	3.2	13.2	
105	26.3	20.2	12.0	9.1	7.8	15.4	
115	24.1	19.5	16.8	14.5	13.5	17.2	
125	21.4	36.3	22.7	22.2	22.0	22.2	
135	48.7	61.9	30.4	30.0	30.1	30.4	
145	77.4	82.4	33.3	33.2	36.1	30.9	
155	81.7	66.2	35.2	29.2	35.0	21.8	
165	55.9	48.0	31.9	23.7	23.5	10.4	
175	33.2	31.4	28.5	27.3	25.6	2.9	
180	27.3	27.3	27.3	27.3	27.3		

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	27.1	9.4
0-40	49.0	17.0
0-60	85.3	29.5
0-90	124.5	43.1
90-120	45.8	15.9
90-130	68.0	23.5
90-150	129.3	44.8
90-180	164.4	56.9
0-180	288.9	100.0

P710010-129-30**Dimming Notes:**

P710010 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.