

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P6537-09

## Burlington

The two-light hanging lantern from the Burlington outdoor collection is constructed from aluminum for durable, weather-resistant performance. A Brushed Nickel finish complements the clear beveled glass. Open bottom design allows individuals to replace lamps without removing any glass shade.

- Brushed Nickel finish.
- Durable aluminum construction.
- Complemented by clear beveled glass.
- Open bottom design allows individuals to easily replace lamps.

**Category:** Outdoor

**Finish:** Brushed Nickel (plated)

**Construction:** Aluminum Construction

**Glass/Shade:** Clear Beveled glass panels



**Square:** 9"  
**Height:** 15-3/4"  
**Overall Ht. W/Chain:** 91"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted  Mounting strap for outlet box included  Six feet of 9 gauge chain supplied  Canopy covers a standard 4" octagonal recessed outlet box  5" W., 0.75" depth	Pre-wired  10 feet of wire supplied  120 V	Quantity:  Two 60w max. Candelabra Base  E12 base phenolic socket	UL-CUL Damp location listed  1 year warranty