

Hide-a-Lite V

Undercabinet Mounted • Damp Location Listed **PROGRESS LED**

P700001-028-30

Description:

Hide-a-Lite V 12" LED Undercabinet

Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- 11.5 in W., 3.3 in ht., 1 in depth
- 6 in of wire supplied


Performance:

Number of Modules	1
Input Power	7.6 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	525/69 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016



Dimensions:

Width: 11-1/2 in
 Depth: 3-3/16 in
 Height: 1-1/8 in




P700001-028-30

Photometrics:

ELECTRICAL DATA	P700001-028-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.064 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P700001-028-30

LED Light Engine: 3000 K 90 CRI
 System Wattage: 7.6
 Fixture delivered lumens: 525
 Fixture Efficacy: 69
 Spacing Criteria: 0.94



Test 17.02412 Test Date 8/31/17

CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION			FLUX		
	0.0	45.0	90.0	135.0	180.0	
0	151	151	151	151	151	
5	157	155	152	144	143	14
15	166	160	146	129	124	41
25	171	159	135	111	102	62
35	169	153	120	89	79	76
45	162	142	101	65	54	80
55	150	126	79	40	32	75
65	133	107	54	20	15	63
75	112	85	28	6	5	47
85	89	61	6	1	1	31
90	76	49	0	0	1	
95	63	37	0	0	0	19
105	40	18	0	0	0	10
115	21	7	0	0	0	4
125	8	2	0	0	0	2
135	2	1	0	0	0	0
145	1	1	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	117	22.4
0-40	193	36.8
0-60	348	66.3
0-90	490	93.3
90-120	33	6.3
90-130	35	6.6
90-150	35	6.7
90-180	35	6.7
0-180	525	100.0

P700001-028-30

Dimming Notes:

P700001-028-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_DELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta

Leviton_Trimatron 6681

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH

Lutron_Ariadni AYL-600P

Lutron_NTLV-600

Lutron_Maestro MAELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.