

Eclipse LED

Wall Mounted • Damp Location Listed **PROGRESS LED**

Description:

Eclipse LED Collection Brushed Nickel One-Light LED Wall Sconce

Specifications:

- Satin White Glass Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 15.25 in W., 7.625 in ht., 1.25 in depth
- 1/8 IP mounting plate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,276/73 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed Meets California Title 24 JA8-2016


P710090-009-30



Dimensions:

Width: 15-1/2 in
 Depth: 4 in
 Height: 7-1/2 in
 H/CTR: 3 in

Satin White Glass Shade
 Width: 12-3/8 in
 Height: 6-3/16 in



P710090-009-30

Dimming Notes:

P710090-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Lutron_Nova T NTELV-300

Lutron_Caseta

Lutron_Ariadni AY-600P

Leviton_Illumatech IPI06-1LZ

Lutron_Lumea LG-603PG

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Skylark Contour CTCL-153P

Lutron_Diva DVCL-153P

Pass & Seymour_Harmony DCL453PTCCCV6

Lutron_Toggler TGCL-153P

Lutron_Maestro MACL-153M

Lutron_Ariadni AYLV-600P

Lutron_Maestro MA-600

Lutron_Nova T NTLV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Leviton_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.