

## One-Light Wall Sconce W/HAL AC LED Module

Wall mounted • Damp location listed



### Description:

Enjoy Progress Lighting's version of a starry night with this LED wall sconce. The geometric panel glass has a Brushed Nickel diffuser and Graphite plate. This puts a beautiful light effect on the wall. The decorative shield features a pinhole pattern resembling a night sky and provides an unexpected and pleasing "twinkle" lighting effect. 90+ CRI, 3000K, 1,211 lumens 71.2 lumens/watt per module source. Dimmable to 10percent with ELV type dimmers. Can be wall mounted also.

### Specifications:

- Graphite (-143) (painted)
- Steel Construction
- Antique Nickel (white painted backside) metal shade, Graphite (white painted backside) metal decorate shade
- LED Module is replaceable (part # 93053641)
- Decorative shield features a pinhole pattern resembling a night sky.
- Enjoy an unexpected and pleasing "twinkle" lighting effect.
- Available with a gently curved metal reflector for grazing effect or a glass diffuser for more general illumination.
- Beyond stands apart as a unique solution for lighting your home or business.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- ENERGY STAR® qualified

### Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	560/33.7 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

## P7101-14330K9

### Images:



### Dimensions:

Square: 10-1/2"

Depth: 3-5/8"

Height: 10-1/2"

H/CTR: 5-1/4"

Antique Nickel (white painted backside)

Width: 10-1/2"

Height: 10-1/2"

Graphite (white painted backside)

Width: 6-1/2"

Height: 6-1/2"

## P7101-14330K9

### Dimming Notes:

---

P7101 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.