

Hide-a-Lite V

Undercabinet Mounted • Damp Location Listed **PROGRESS LED**

Description:

Hide-a-Lite V 24" LED Undercabinet

Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- 23.5 in W., 3.3 in ht., 1 in depth
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	14.6 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	980/67 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016

P700003-020-30



Dimensions:

Length: 23.5 in
 Width: 3-3/16 in
 Height: 1-1/8 in



P700003-020-30

Photometrics:

ELECTRICAL DATA	P700003-020-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.123 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P700003-020-30


LED Light Engine: 3000 K 90 CRI
 System Wattage: 14.6
 Fixture delivered lumens: 980
 Fixture Efficacy: 67
 Spacing Criteria: 0.93

CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION					FLUX
	0.0	45.0	90.0	135.0	180.0	
0	279	279	279	279	279	
5	294	288	285	268	266	26
15	313	297	274	239	230	76
25	322	297	254	204	187	116
35	320	286	223	161	142	140
45	308	266	185	116	96	148
55	285	237	144	72	56	139
65	255	202	99	33	25	117
75	217	161	52	9	8	88
85	171	117	9	1	2	60
90	148	94	0	0	1	
95	125	72	0	0	0	37
105	80	35	0	0	0	20
115	42	13	0	0	0	9
125	17	3	0	0	0	3
135	4	1	0	0	0	1
145	1	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	218	22.3
0-40	358	36.6
0-60	645	65.9
0-90	911	92.9
90-120	65	6.7
90-130	68	7.0
90-150	69	7.0
90-180	69	7.1
0-180	980	100.0



Test 17.02424 Test Date 09/06/17

P700003-020-30

Dimming Notes:

P700003-020-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_DELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta

Leviton_Trimatron 6681

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH

Lutron_Ariadni AYL-600P

Lutron_NTLV-600

Lutron_Maestro MAELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.