

Hide-a-Lite V

Undercabinet Mounted • Damp Location Listed **PROGRESS LED**

Description:

Hide-a-Lite V 36" LED Undercabinet

Specifications:

- White Polycarbonate Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- 35.5 in W., 3.3 in ht., 1 in depth
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	21.1 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,517/72 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	Meets California Title 24 JA8-2016

P700004-020-30



Dimensions:

Length: 35-1/2 in
 Width: 3-3/16 in
 Height: 1-1/8 in




P700004-020-30

Photometrics:

ELECTRICAL DATA	P700004-020-30
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.177 A
Power Factor	Greater than 0.90
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P700004-020-30

LED Light Engine: 3000 K 90 CRI
 System Wattage: 21.1
 Fixture delivered lumens: 1517
 Fixture Efficacy: 72
 Spacing Criteria: 0.96



CANDELA DISTRIBUTION

CANDELA	DISTRIBUTION					FLUX
	0.0	45.0	90.0	135.0	180.0	
0	441	441	441	441	441	
5	465	455	445	424	423	42
15	495	470	429	381	369	120
25	508	468	398	326	306	183
35	503	450	353	262	236	223
45	481	416	297	190	161	235
55	443	369	232	118	90	219
65	391	313	158	54	37	182
75	328	247	83	13	10	135
85	257	172	16	1	2	89
90	219	135	0	0	1	
95	178	100	0	0	0	51
105	106	41	0	0	0	25
115	47	11	0	0	0	9
125	16	3	0	0	0	3
135	4	1	0	0	0	1
145	1	1	0	0	0	0
155	0	0	0	0	0	
165	0	0	0	0	0	
175	0	0	0	0	0	0
180	0	0	0	0	0	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	345	22.8
0-40	568	37.5
0-60	1022	67.4
0-90	1428	94.1
90-120	85	5.6
90-130	88	5.8
90-150	89	5.9
90-180	89	5.9
0-180	1517	100.0

Test 17.02425 Test Date 09/05/17

P700004-020-30

Dimming Notes:

P700004-020-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_DELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta

Leviton_Trimatron 6681

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH

Lutron_Ariadni AYL-600P

Lutron_NTLV-600

Lutron_Maestro MAELV-600

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.