

Project:

Fixture Type:

Location:

Contact:

Phase 4 LED

Wall Mounted • Damp Location Listed PROGRESS LED



Description:


Phase 4 Collection 16 in. Matte Black Small Modern Integrated 3CCT Integrated LED Linear Vanity Light

Specifications:

- Diffused Plastic Flat Square/Rectangular
- Dimmable to 10% brightness (See Dimming Notes)
- $\cdot\,$ Canopy covers a standard 4" recessed outlet box: 4.5 in W., 4.5 in ht., 1.26 in depth
- Mounting backplate for outlet box included
- 10 in of wire suppliedAmericans With Disabilities Act (ADA) compliant
- X

Performance:

Input Power	11 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	827/75 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR [®] qualified
	Meets California Title 24 JA8-2016



Dimensions:

Width: 16 in Extends: 2 in Height: 4-3/4 in



Phase 4 LED

Wall Mounted • Damp Location Listed PROGRESS LED

Photometrics:

ELECTRICAL DATA	P710110-31M-CS
Input Voltage	120 V
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P710110-31M-CS

-Energy



Phase 4 LED

Wall Mounted • Damp Location Listed PROGRESS LED



 ${\sf P710110\text{-}31M\text{-}CS}$ is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

aton SAL06P
eviton 6681
viton IPI06-1LZ
viton 6672
eviton 6674
utron NTEVL-300
utron DVELV-300P
utron DVCL-253P
utron Caseta Wireless
evices IDEV009
utron AYCL-153P
utron SCL-153P
utron TGCL-153-PH-WH
utron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P710110-31M-CS