

Project:

Fixture Type:

Location:

Contact:

## Intrinsic

Recessed Mounted • Damp Location Listed



P800018-031-CS



### **Description:**

Intrinsic Collection 6 " 5-CCT Black LED Eyeball Trim for Recessed Housings

### **Specifications:**

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied

#### **Performance:**

Input Power	8 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	698/87 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 20



#### **Dimensions:**

Diameter: 7-11/16 in Height: 3-15/16 in



The adjustable light source can be aimed allowing the trim to be used as a standard downlight, accent light, wall wash or sloped ceiling light.



# Intrinsic

Recessed Mounted • Damp Location Listed



#### **Photometrics:**

P800018-031-CS

ELECTRICAL DATA P800018-031-CS

Input Voltage 120 V
Input Frequency 60 Hz
THD <20%

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature -40 °C to 40 °C

Dimming Yes\*

\*See Dimming Notes for more information



## Intrinsic

Recessed Mounted • Damp Location Listed



#### **Dimming Notes:**

P800018-031-CS is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

# P800018-031-CS

#### **Dimming Controls:**

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.