

LED CTC COMM

Flush-Mount Mounted • Damp Location Listed PROGRESS LED



Description:

One-Light Urban Bronze LED close-to-ceiling. Surface mount oval with clean modern lines and white acrylic diffuser. DC LED light engine with 2649 delivered lumens at 3000K and 90+ CRI.

Specifications:

- White acrylic Diffuser
- Urban Bronze finish.
- Steel construction.
- Dimmable to 10% brightness with many Forward and Reverse Phase dimmers.
- 3000k color temperature.
- TM-21 54,000 hour life.
- Meets California Title 24 - JA8 - 2016.
- 2,649 lumens (delivered).
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" recessed outlet box: 32.25 in W., 0.375 in ht., 17.875 in depth
- Ceiling pan
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	39 W
Input Voltage	120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	2,649/67.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	ETL Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


P7251-17430K9



Dimensions:

Length: 32-1/2 in
Width: 18 in
Height: 4-3/4 in

White acrylic Diffuser
Width: 16-13/16 in




Photometrics:

P7251-17430K9

ELECTRICAL DATA	P7251-17430K9
Input Voltage	120-277 VAC
Input Frequency	50/60 Hz
Input Current	0.327 A
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-current, short-circuit protected	
*See Dimming Notes for more information	

P7251-17430K9
 LED Light Engine: 3000 K 90 CRI
 System Wattage: 39 max.
 Fixture delivered lumens: 2649
 Fixture Efficacy: 67.9
 Spacing Criteria: 1.0

ZONAL LUMEN SUMMARY		
ZONE	LUMENS	%FIXT
0-30	178	17.3
0-40	296	28.9
0-60	556	54.2
0-90	836	81.4
90-120	130	12.6
90-130	156	15.2
90-150	185	18
90-180	191	18.6
0-180	1027	100.0



Test 17.00401 Test Date 02/09/17

P7251-17430K9

Dimming Notes:

P7251-17430K9 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T VTELV-300

Lutron_Diva DVELV-300P

Lutron_Caseta Wireless

Leviton_Renoir II AWRMG-EAW

Lutron_Nova N-600

Lutron_Diva DVCL-253P-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.