

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____



Circline fluorescent

P7373-30

Hard-Nox

Two-light flush mount with white acrylic diffuser mounts to baked enamel ceiling pan. Twist on installation with a single locking thumb screw. UL approved for damp locations. Rapid start 120V NPF ballast. Ceiling or wall mount. ADA compliant when wall mounted. Uses one FC12T9 32W and one FC16T9 40W lamps.

Diameter: 18-3/4"
Height: 4-1/4"

- Two-light flush mount.
- White acrylic diffuser mounts to baked enamel ceiling pan.
- Twist on installation with a single locking thumb screw.
- Ceiling or wall mount.
- UL approved for damp locations.
- Ceiling or wall mount.

Category: Outdoor

Finish: White (baked enamel)

Construction: Steel Construction

Glass/Shade: White acrylic cloud diffuser

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or ceiling mounted Mounting screws for outlet box included Ceiling pan covers a standard 4" octagonal recessed outlet box 8.0625" W., 0.25" ht., 8.0625" depth	Pre-wired 6" of wire supplied 120V HPF rapid start 120 V	Quantity: One 32w max. FC12T9 4-pin circline base lamp holders One 40w FC16T9 4-pin circline base	UL-CUL Damp location listed 1 year warranty