

One-Light Close-To-Ceiling

Wall or ceiling mounted • Damp location listed



Description:

LED ceiling mount with white acrylic diffuser and regressed chassis. Wall or ceiling mount. 3000K, 90+ CRI, 1,211 lumens source. Dimmable to 10 percent with ELV type dimmers.

Specifications:

- White (-30) (painted)
- Steel Construction
- White acrylic diffuser
- LED Module is replaceable (part # 93053641)
- One-light LED flush mount.
- White acrylic diffuser mounts to baked enamel ceiling pan.
- Twist on installation with a single locking thumb screw.
- Ceiling or wall mount.
- UL approved for damp locations.
- Ceiling or wall mount.
- 1,211 lumens (source).
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified

Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82)
Lumens/LPW (Delivered)	801/49.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

P7376-3030K9

Images:



Dimensions:

Diameter: 11"
Height: 3-1/16"

Photometrics:

P7376-3030K9

ELECTRICAL DATA		P7376-3030K9
Input Voltage		120 V
Input Frequency		60 Hz
Input Current		0.142 A
Input Power		17
Power Factor		Greater than 0.90
THD		<20%
FCC		Meets FCC Title 47, Part 15 Class B
Operating Temperature		-30 °C to 30 °C
Dimming		Yes*

*See Dimming Notes for more information

P7376-3030K9


LED Light Engine: 3000 K 90 CRI

System Wattage: 17

Fixture delivered lumens: 801

Fixture Efficacy: 49.8

Spacing Criteria: 1.4



CANDELA DISTRIBUTION

DEG	CANDELA	LUMENS
0	175	
5	175	17
15	172	49
25	165	76
35	153	96
45	136	105
55	114	102
65	89	88
75	61	64
85	37	41
90	32	
95	31	34
105	30	32
115	29	29
125	27	24
135	25	19
145	22	14
155	17	8
165	12	4
175	10	1
180	10	

ZONAL LUMEN SUMMARY

ZONE	LUMENS	%FIXT
0-30	142	17.7
0-40	237	29.6
0-60	444	55.4
0-90	638	79.6
90-120	94	11.7
90-130	118	14.7
90-150	151	18.8
90-180	163	20.4
0-180	801	100.0

Test 15.00949 Test Date 06/04/15

P7376-3030K9

Dimming Notes:

P7376 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Maestro	MAELV-600
Lutron	spacer/system	SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.