

Project:			
Fixture Type:			
Location:			
Contact:			

# P8080 SERIES 4IN LED New Construction and Remodel · Wet location listed

PROGRES	SS LED)



# **Description:**

The P8080 is ideal for use in both new construction as well as remodel/retrofit. Light output is comparable to that of a typical 50W incandescent downlight, providing up to 75% energy savings. The P8080 is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard incandescent recessed housings.

## **Specifications:**

- Available in White, Bronze, Black and Brushed Nickel
- Diffused polycarbonate lens controls direct glare from the LEDs
- Easy "Push and Twist" installation with (3) friction spring clips
- Can be installed in most competitors 4" recessed housings
- · Dimmable to 10% with many Triac/Forward Phase dimmers
- Suitable for use in IC or NON-IC Applications
- · Provided with quick link for use with E26 Edison Base adapter
- · Meets California Title 24 JA8 2016.
- · ENERGY STAR® qualified



P8080-28-30K




### **Performance:**

Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	651/72 (LM-79)
ССТ	3000 K
CRI	90
Life (hours)	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Wet location listed
	ENERGY STAR® qualified
	Meets California Title 24 - JA8 - 2016

### **Dimensions:**

Images:

- (A) Outside Diameter: 5"
- (B) Height: 3-1/4"
- (C) Inside Diameter: 4"
- (D) Light Emitting Surface (LES): 2.75"



# Catalog number:

Base P8080 Finish


Color Temp 30K - 3000 K

CRI **BLANK - 90** 

09 - Brushed Nickel 20 - Antique Bronze

28 - Satin White

31 - Black





P8080 SERIES 4IN LED New Construction and Remodel · Wet location listed





### P8080-28-30K **Photometrics:**

ELECTRICAL DATA	P8080-28-30K
Input Voltage	120 V
Input Frequency	60 Hz
Input Current	0.07 A
Power Factor	>0.90
THD	<20%
EMI Filtering	FCC 47CFR
	Part 15, Class B
Operating Temperature	-30 °C to 30 °C
Dimming	Yes*
Over-voltage, over-currer	nt, short-circuit protected


### P8080-28-30K

LED Light Engine: 3000 K, 90 CRI

System Wattage: 9

Fixture Delivered Lumens: 651

Fixture Efficacy: 72 Spacing Criteria: 1.0



ZONAL LUMEN SUMMARY					
Zone	Zone Lumens	Total Lumens	% Luminaire		
0-10	28.24	28.24	4.97		
10-20	78.77	107	18.9		
20-30	113.1	220.1	38.8		
30-40	125.3	345.3	60.8		
40-50	112.2	457.4	80.6		
50-60	74.99	532.5	93.8		
60-70	31.03	563.4	99.3		
70-80	4.063	67.6	100		
80-90	0.0169	567.6	100		

<sup>\*</sup>See Dimming Notes for more information



P8080 SERIES 4IN LED New Construction and Remodel · Wet location listed



P8080-28-30K

## **Dimming Notes:**

P8080 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

### **Triac/Forward Phase Controls**

Lutron AYCL-153P

Lutron TGCL-153P

Leviton 6672

Leviton 6674

Leviton 6681

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.