

## Intrinsic

Recessed housing Mounted • Damp Location Listed PROGRESS LED



### Description:

Intrinsic Collection 4" Adjustable Eyeball 5-CCT Recessed Trim

### Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	1 Recessed
Input Power	8 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	801/100 (LM-79)
CCT	2700 K, 3000 K, 3500 K, 4000 K, 5000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed ENERGY STAR® qualified Meets California Title 20

# P800022-028-CS



### Dimensions:

Diameter: 5-11/16 in  
Height: 3-3/16 in

**Dimming Notes:**

---

P800022-028-CS is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls:**

---

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

# P800022-028-CS