

roject:		
ixture Type:		
ocation:		

P810041-028-30

# Standby LED

Ceiling Flush Mounted • Wet Location Listed PROGRESS LED

#### **Description:**

Standby Collection 7.75 in. White Surface Mount Motion Detection LED Light

## **Specifications:**

- · Diffused Polycarbonate Lens
- · Dimmable to 10% brightness (See Dimming Notes)
- Housing covers a standard 4" recessed outlet box

#### **Performance:**

Input Power	14 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	975/74 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed



### **Dimensions:**

Diameter: 7-11/16 in Height: 1-3/8 in





**PROGRESS** LIGHTING

Standby LED

Ceiling Flush Mounted • Wet Location Listed PROGRESS LED

Standby LED

Ceiling Flush Mounted • Wet Location Listed PROGRESS LED

### **Photometrics:**

P810041-028-30

ELECTRICAL DATAP810041-028-30Input Voltage120 VACInput Frequency60 HzTHD<20%</td>

EMI/RFI FCC Title 47, Part 15, Class B

Operating Temperature -25 °C to 50

Dimming Yes\*

Over-voltage, over-current, short-circuit protected \*See Dimming Notes for more information

### **Dimming Notes:**

P810041-028-30

P810041-028-30 is designed to be compatible with many ELV ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls:**

Lutron NTEVL-300, Lutron DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.