

P8176 SERIES

5IN LED Eyeball • Damp location listed



Description:

The P8176 is ideal for use in both new construction as well as remodel/retrofit. Light output is comparable to that of a 65W incandescent lamp. The 8176 is equipped with both Edison base adapter and quick link connector allowing easy installation in many standard incandescent recessed housings.

Specifications:

- Black finish.
- Diffused polycarbonate lens controls direct glare from the LEDs.
- Easy "Push and Twist" installation with (3) friction spring clips.
- Can be installed in most competitors 5" recessed housings.
- Dimmable to 10% with many Triac/Forward Phase dimmers.
- Suitable for use in IC or NON-IC Applications.
- Provided with quick link for use with E26 Edison Base adapter.
- This product is not available for sale into the State of California.
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	702/78 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

Images:


P8176-31-30K



Dimensions:

(A) Outside Diameter: 6.50"

(B) Height: 3.8"



P8176-31-30K

Dimming Notes:

P8176 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron AYCL-153P

Lutron TGCL-153P

Leviton 6672

Leviton 6674

Leviton 6681

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.