



Temporary Cutout Load Break Tool, 15/27kV

by CHANCE Utility
Catalog ID: PSC6010348

CUTOUT, TEMPORARY 27KV POLY LOADBREAK, This tool provides a temporary means of connecting and disconnecting equipment or circuits under load conditions. This tool design does not have a fuse and does not provide protection for fault or overcurrent conditions. Hot parts are identical to Chance Type C cutouts, including the tubular-copper disconnect blade. The tool simply clamps onto primary conductor with a Grip-All clampstick. Brass stud at lower end accepts clamp on temporary tap jumper. An arc-chute-type interrupter gives the tool its excellent loadbreak capability. To interrupt load currents, the device makes use of a stainless-steel auxiliary blade within a Delrin® arc chute. This self-contained loadbreak device operates by a simple disconnect stick. No special or portable tools are required to operate the unit. To break the current, just insert a disconnect stick into the operating ring and rapidly open the device. In the process of opening, the spring-loaded auxiliary blade snaps out through the arc chute to elongate, cool and extinguish the confined arc. This loadbreaking operation is independent of the disconnect stick speed. To provide a clearly visible break, the disconnect blade hangs in approximately a vertical position.

Product Details

General

Style	Load Disconnect
UPC	096359395645

Dimensions

Weight	30.87 lb
--------	----------

Electrical Ratings

Voltage Rating	27000 V
----------------	---------

Conductor Related

Conductor Diameter (Main) - Maximum	1.16 in
-------------------------------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com