

# PCISW - 32T8 SERIES

Stairwell Luminaire

## Specifications:

### Features:

- Energy saving luminaire with integrated occupancy controls
- Stairwell light control offers safety and security
- Ideal for stairwells, parking structures, restrooms and areas where maximum light levels are not needed when area is unoccupied
- White aluminum body allows for greater heat dissipation
- Occupancy sensor has a 360° coverage area at a height of 10 ft and a 2:1 radius to height ratio coverage pattern
- Tool-less access to ballast for ease of maintenance
- Can be surface mounted, wall mounted or suspended
- Standard class "P", thermally protected, sound rated A, autoresetting HPF ballast
- Fail safe operation switches light level to 100% if sensor is damaged
- Universal input voltage 120-277 VAC, 50/60Hz


### Images:



### Compliances:

PCISW – 32T8 Series are built to UL 1598 standards and bear appropriate CSA c/UL labels. Damp location labeling is standard.

### Dimensions:



### Catalog number:

Base	Lamp Type	Size
PCISW	32T8 - T8, 32 Watts	4 - 4'

# PCISW - 32T8 SERIES

Stairwell Luminaire

## Photometric Data:

PCISW-32T8-4	
Ballast Factor	1.00
Lamp	F32T8
Lumens per Lamp	2383
Watts	100
Mounting	SURFACE
Shielding Angle	N/A
Spacing Criterion	0° = 1.27 90° = 1.41
Luminous Option (LxWxH)	3.99' x 0.50' x 0.34'

Zonal Lumen Summary PCISW-32T8-4			
Zone	Lumens	% Lamp	%Fixt
0-30	1041	14.6	20.1
0-40	1742	24.4	33.7
0-60	3241	45.3	62.6
0-90	4599	64.3	88.9
0-180	5175	72.4	100.0

Energy Data PCISW-32T8-4	
Total Luminance Efficiency	72.4%
Total Luminance per Watt	N/A
ANSI/IESNA RP-1-2004 Compliance	Noncompliant

INDOOR CANDELA PLOT

