

PT24-2.5

by CMC
Catalog ID: PT24-2.5



Compression connectors, Aluminum pin terminal

- Tinned copper rod factory crimped into an aluminum compression sleeve. Cavities are pre-filled with electrical joint compound and capped
- Pin terminals are widely used in clamp-type plated bronze connectors, common to pole-type transformers, disconnect switches, cutouts and lightning arrestors, to allow aluminum conductors to be connected. The transition from copper to aluminum is made within a sealed compression joint to assure protection from bi-metallic corrosion.

Product Details

General

Material	Aluminum
UPC	192663118960

Dimensions

Equivalent Pin Size	4 Sol.
Length	4.625 in
Length - Pin	2.5 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor - ACSR Str Size	2 AWG
Conductor Diameter - Maximum	0.328 in
Conductor Diameter - Minimum	0.268 in
Conductor Diameter Range	0.268 - 0.328



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

