


ER7-40 | Type GL Grid Resistor

By Powerohm
Catalog # [GL30](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 7.8 Ohms 30 A

Features

- Continuous Wattage:7020

General

Max. Vibration	26.5
Nominal Current (A)	7020
Resistance Ohms	7.8 Ohm
Size	11
System Voltage	600 VAC
Type	Grid Resistor Type GL

Dimensions

Depth	12.75 in
Length	26.5 in
Weight	28 lb
Width	11 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Maximum Current Rating Amps Continuous	30 Amps
Wattage	7020 W