


GL37-D | Type GL Grid Resistor

By Powerohm Resistors
Catalog # [GL50-D](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 5.88 Ohms 50 A

Features

Continues Wattage:14700

General

Resistance Ohms	5.88 Ohm
System Voltage	600 VAC
Type	Grid Resistor Type GL

Dimensions

Depth	21.5 in
Length	26.5 in
Weight	45 lb
Width	19.44 in

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Maximum Current Rating Amps	50 Amps
Continuous Wattage	14700 W

Product Assets