


GL37-D | Type GL Grid Resistor

By Powerohm
Catalog # [GL50-D](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 5.88 Ohms 50 A

Features

- Continuous Wattage:14700

General

| | |
|-----------------|-----------------------|
| Resistance Ohms | 5.88 Ohm |
| System Voltage | 600 VAC |
| Type | Grid Resistor Type GL |

Dimensions

| | |
|--------|----------|
| Depth | 21.5 in |
| Length | 26.5 in |
| Weight | 45 lb |
| Width | 19.44 in |

Electrical Ratings

| | |
|---|---------|
| Amperage Rating | 50 A |
| Current / Amperage Rating | 50 A |
| Maximum Current Rating Amps Continuous | 50 Amps |
| Wattage | 14700 W |