


GL50 | Type GL Grid Resistor

By Powerohm
Catalog # [GL73](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 1.22 Ohms 73 A

Features

- Continuous Wattage:6501

General

Max. Vibration	26.5
Nominal Current (A)	6500
Resistance Ohms	1.22 Ohm
Size	10
System Voltage	600 VAC
Type	Grid Resistor Type GL

Dimensions

Depth	12.75 in
Length	26.5 in
Weight	29 lb
Width	11 in

Electrical Ratings

Amperage Rating	73 A
Current / Amperage Rating	73 A
Maximum Current Rating	73 Amps
Amps Continuous	
Wattage	6501 W