


## GL41 | Type GL Grid Resistor

By Powerohm  
Catalog # [GL57](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 2.02 Ohms 57 A

### Features

- Continuous Wattage:6563

### General

Max. Vibration	26.5
Nominal Current (A)	6560
Resistance Ohms	2.02 Ohm
Size	10
System Voltage	600 VAC
Type	Grid Resistor Type GL

### Dimensions

Depth	12.75 in
Length	26.5 in
Weight	27 lb
Width	11 in

### Electrical Ratings

Amperage Rating	57 A
Current / Amperage Rating	57 A
Maximum Current Rating	57 Amps
Amps Continuous	
Wattage	6563 W