


GL46 | Type GL Grid Resistor

By Powerohm Resistors
Catalog # [GL63](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 1.82 Ohms 63 A

Features

Continues Wattage:7224

General

Max Vibration	26.5
Nominal Current (A)	7220
Resistance Ohms	1.82 Ohm
Size	10
System Voltage	600 VAC
Type	Grid Resistor Type GL

Dimensions

Depth	12.75 in
Length	26.5 in
Weight	26 lb
Width	11 in

Electrical Ratings

Amperage Rating	63 A
Current / Amperage Rating	63 A
Maximum Current Rating Amps	63 Amps
Continuous	
Wattage	7224 W

Product Assets