


GL85-T | Type GM Grid Resistor

By Powerohm
Catalog # GM110-T



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GM Grid Resistor 1.404 Ohms 110 A

Features

- Continuous Wattage:16988

General

Max. Vibration	26.5
Resistance Ohms	1.404 Ohm
System Voltage	600 VAC
Type	Grid Resistor Type GM

Dimensions

Depth	29 in
Length	26.5 in
Weight	78 lb
Width	27.75 in

Electrical Ratings

Amperage Rating	110 A
Current / Amperage Rating	110 A
Maximum Current Rating Amps Continuous	110 Amps
Wattage	16988 W