


## GL91-D | Type GM Grid Resistor

By Powerohm  
Catalog # [GM120-D](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GM Grid Resistor 0.842 Ohms 120 A

### Features

- Continuous Wattage:1215

### General

Max. Vibration	26.5
Resistance Ohms	0.842 Ohm
System Voltage	600 VAC
Type	Grid Resistor Type GM

### Dimensions

Depth	21.5 in
Length	26.5 in
Weight	55 lb
Width	19.44 in

### Electrical Ratings

Amperage Rating	120 A
Current / Amperage Rating	120 A
Maximum Current Rating Amps Continuous	120 Amps
Wattage	12125 W