


GL57-T | Type GL Grid Resistor

By Powerohm Resistors
Catalog # [GL80-T](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GL Grid Resistor 3.09 Ohms 80 A

Features

Continues Wattage:19776

General

Max Vibration	26.5
Resistance Ohms	3.09 Ohm
System Voltage	600 VAC
Type	Grid Resistor Type GL

Dimensions

Depth	29 in
Length	26.5 in
Weight	89 lb
Width	27.75 in

Electrical Ratings

Amperage Rating	80 A
Current / Amperage Rating	80 A
Maximum Current Rating Amps	80 Amps
Continuous Wattage	19776 W

Product Assets