

GL91 | Type GM Grid Resistor

By Powerohm Resistors
Catalog # [GM120](#)



Powerohm’s Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GM Grid Resistor 0.421 Ohms 120 A

Features

Continues Wattage:6062

General

Catalog Number	GM120
Max Vibration	26.5
Nominal Current (A)	6060
Resistance Ohms	0.421 Ohm
Size	11
System Voltage	600 VAC
Type	Grid Resistor Type GM

Dimensions

Depth	12.75 in
Length	26.5 in
Weight	29 lb
Width	11 in

Electrical Ratings

Amperage Rating	120 A
Current / Amperage Rating	120 A
Maximum Current Rating Amps	120 Amps
Continuous	
Wattage	6062 W

Product Assets

[Specifications - GM120](#)