


GM120 | Type GM Grid Resistor

By Powerohm
Catalog # [GM165](#)



Powerohm's Grid Resistors are most commonly used for motor acceleration and braking, but are also suitable for dynamic braking of variable frequency drives, load banks, harmonic filtering and neutral grounding applications. Resistor banks feature stainless steel stamped elements double insulated from supporting end frames with all silicone mica. The elements are offset and welded to eliminate current carrying washers and unwanted breaks in the current path. Type GM Grid Resistor, 165 A, 0.24 Ohms, 600 VAC, 6534 W Powerohm Grid Resistor

Features

- Continuous Wattage:6534

General

Max. Vibration	26.5
Nominal Current (A)	6530
Resistance Ohms	0.24 Ohm
Size	8
System Voltage	600 VAC
Type	Grid Resistor Type GM

Dimensions

Depth	12.75 in
Length	26.5 in
Weight	33 lb
Width	11 in

Electrical Ratings

Amperage Rating	165 A
Current / Amperage Rating	165 A
Maximum Current Rating	165 Amps
Amps Continuous	
Wattage	6534 W