

# Fan-Cooled Braking Resistor

By Powerohm Resistors

Powerohm Type LB Resistors including portable and freestanding Fan-Cooled Braking Resistors.



## Features

- Nominal Voltage Ratings of 240/480 VAC, 480 VAC and 600 VAC
- Power Ratings Ranging from 200 kilowatts to 2500 kilowatts
- Heavy duty enclosures with galvanized and powder coated finish
- PowerDyne™ load elements with stainless steel rod supports
- Remote control panel with standard NEMA-12 control enclosure
- Outdoor NEMA-3R enclosure designs
- Multi-compartment enclosure isolates controls and power connections from load elements and blower compartment

- Thermostatically controlled strip heater within the Fan-Cooled Braking Resistor relay compartment
- Built-in forklift channels for easy installation and lifting
- Multiple cable entry points with aluminum gland plates included
- Fused circuit protection for all control and power circuits
- Industry leading safety features, conservative designs, long life, and value

## Product Assets

[Specifications - Load Bank Resistors](#)