

R2-0.75A02 | Powerohm Braking Resistor

By Powerohm Resistors
Catalog # [R2-0.75A02](#)

230 V 0.75 H P 100% Braking Torque 20% Duty 250 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

General

Application	Powerohm
Available Options	Mill Galvanized
Braking Torque	100 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE1
Horsepower - Maximum	0.75
Nominal Current (A)	552
Resistance Ohms	250 Ohm
System Voltage	230 V

Dimensions

Depth	5 in
Length	12.375 in
Width	5 in