

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-100A10](#)



Type R2 1.9 Ohms Braking Resistor For 230 V 100 H P 100%
Braking Torque 100% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R2-100A10
Duty Cycling	100 %
Enclosure Type	ED6
Horsepower - Maximum	100
Resistance Ohms	1.9 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

Product Assets

[Specifications - R2-100A10](#)