

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-250A02](#)



Type R2 0.8 Ohms Braking Resistor For 230 V 250 H P 100%
Braking Torque 20% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R2-250A02
Duty Cycling	20 %
Enclosure Type	ED4
Horsepower - Maximum	250
Resistance Ohms	0.8 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R2-250A02](#)