

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-10A01](#)



Type R2 19 OhmsBraking Resistor For 230 V 10 H P 100%
Braking Torque 10% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R2-10A01
Duty Cycling	10 %
Enclosure Type	GCE2
Horsepower - Maximum	10
Resistance Ohms	19 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R210A01](#)