

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-2A03](#)



Type R2 95 Ohms Braking Resistor For 230 V 2 H P 100% Braking
Torque 30% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R2-2A03
Duty Cycling	30 %
Enclosure Type	GCE2
Horsepower - Maximum	2
Resistance Ohms	95 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

Product Assets

[Literature - Dynamic Braking Resistors](#)
[Specifications - R2-2A03](#)