

R4-10B02 | Powerohm Braking Resistor

By Powerohm
Catalog # [R4-10B02](#)

460 V 10 H P 150% Braking Torque 20% Duty 50 Ohms



Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

Application

Powerohm

General

Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	20 %
Enclosure Style	NEMA 1
Enclosure Type	GCE8
Horsepower - Maximum	10
Resistance Ohms	50 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

Dimensions

Depth	5 in
Length	19.375 in
Width	13 in