

# R4-15A05 | Powerohm Braking Resistor

By Powerohm  
Catalog # [R4-15A05](#)

460 V 15 H P 100% Braking Torque 50% Duty 50 Ohms



## Features

- The resistor dissipates regenerated power to keep the bus voltage from exceeding the rated limit of the drive
- Provide Controlled Braking

## Application

Powerohm

## General

Available Options	Mill Galvanized
Braking Torque	150 %
Duty Cycling	50 %
Enclosure Style	NEMA 1
Enclosure Type	GCE24
Horsepower - Maximum	15
Nominal Current (A)	11185.5
Resistance Ohms	50 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

## Dimensions

Depth	10 in
Length	26.375 in
Width	13 in