

# Type R2 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R2-25B03](#)



Type R2 5 OhmsBraking Resistor For 230 V 25 H P 150% Braking  
Torque 30% Duty Variable Frequency Drives

**Features**

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

**Application**

Powerohm

**General**

|                      |                     |
|----------------------|---------------------|
| Braking Torque       | 150 %               |
| Catalog Number       | R2-25B03            |
| Duty Cycling         | 30 %                |
| Enclosure Type       | GCE24               |
| Horsepower - Maximum | 25                  |
| Resistance Ohms      | 5 Ohm               |
| System Voltage       | 230 V               |
| Type                 | R2 Braking Resistor |

**Product Assets**

[Literature - Dynamic Braking Resistors](#)  
[Specifications - R225B03](#)