

# Type R4 Dynamic Braking Resistor

By Powerohm Resistors  
Catalog # [R4-1B05](#)



Type R4 500 OhmsBraking Resistor For 460 V 1 H P 150%  
Braking Torque 50% Duty Variable Frequency Drives

**Features**

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

**Application**

Powerohm

**General**

Braking Torque	150 %
Catalog Number	R4-1B05
Duty Cycling	50 %
Enclosure Type	GCE2
Horsepower - Maximum	1
Resistance Ohms	500 Ohm
System Voltage	460 V
Type	R4 Braking Resistor

**Product Assets**

[Specifications - R4-1B05](#)