

Type R2 Dynamic Braking Resistor

By Powerohm Resistors
Catalog # [R2-75A05](#)



Type R2 2.7 OhmsBraking Resistor For 230 V 75 H P 100%
Braking Torque 50% Duty Variable Frequency Drives

Features

- Standard Galvanized Material Enclosure
- Indoor or Outdoor Rated Enclosure
- UL or CE Certification Option
- Normally Closed or Normally Open Thermal Switch Option

Application

Powerohm

General

Braking Torque	100 %
Catalog Number	R2-75A05
Duty Cycling	50 %
Enclosure Type	ED4
Horsepower - Maximum	75
Resistance Ohms	2.7 Ohm
System Voltage	230 V
Type	R2 Braking Resistor

Product Assets

[Specifications - R2-75A05](#)